

PRODUCT INFORMATION

NOVATECH

ITP 100x40-Ø15 HL40 cv

EAN 4031582383867



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity at 6 km/h	240 kg
Electric Conductive	No
Stainless	No
Load capacity Static	600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.46 kg

WHEEL

Tread profile	convex
Body material	Aluminium
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Wheel Color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	40 mm
Axle Hole Diameter	15 mm
Hub Length	40 mm
Body width	40 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Suitable for	pimespo_still_wagner

NOVATECH

ITP 100x40-Ø15 HL40 cv


EAN 4031582383867

Order number 00830212

Product Drawings



BETTER MOBILITY. BETTER LIFE.




PRODUCT INFORMATION

NOVATECH

ITP 100x40-015 HL40 cv

EAN 4031582383967

Order number 00830212



BETTER MOBILITY. BETTER LIFE.