

AGILA CARE

2476YGO125R36-32S30 4XM6

EAN 4031582342413



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---|
| Product name | Agila care |
| Type | Swivel castor with central , total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 220.46 lb |
| Electric conductive | ✓ |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 6.42 in |
| Overall weight | 1.98 lb |

WHEEL

| | |
|-----------------------|---|
| Body material | Polypropylene, electric conductive |
| Tread material | Thermoplastic rubber, electric-conductive |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 4.92 in |
| Tread width | 1.26 in |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|---------------------|
| Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 1.61 in |
| Swivel radius | 4.07 in |
| Swivel interference | 8.15 in |

FITTING

| | |
|---------------|--|
| Fitting type | Stem with cam hole for profile bars, short version |
| Bolt diameter | 1.26 in |
| Bolt length | 2.01 in |

AGILA CARE

2476YGO125R36-32S30 4XM6

EAN 4031582342413



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

