

AGILA

2471DIK150R05-28

EAN 4031582301342



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Agila
Tip	Okreni Tocak sa usmerena kocnica
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Sveukupna visina	188 mm
Ukupna težina	1,773 kg

TOCAK

Materijal za telo	Čelik lista
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	konusi lezaj
stitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	32 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

KUCISTE

Materijal	Čelični list, srednji
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	36 mm
Otpor okretanju	262 mm

PRILAGOĐAVANJE

Tip uklapanja	stablo, okrugla
Prečnik sraf	28 mm
Dužina sraf	45 mm

AGILA

2471DIK150R05-28

EAN 4031582301342



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

