

PURETECH

DIK 150X32-Ø8,1

EAN 4031582070170
Order number 00000163



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Sheet Steel |
| Tread material | Solid rubber, non-marking |
| Bearing | Cone ball bearing |
| Wheel color | Blue passivated |
| Threadguards | With threadguard |
| Diameter | 150 mm |
| Tread width | 32 mm |
| Axle hole diameter | 8 mm |
| Hub length | 36 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 80 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Puretech |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 85 °C |
| Overall weight | 0.896 kg |

PURETECH

DIK 150X32-Ø8,1

EAN 4031582070170
Order number 00000163



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

