

AGILA

2478DYK075P60-67X60

EAN 4031582344523



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Agila
Type	Fixed caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	121.25 lb
Electric conductive	Yes
Stainless	no
Load capacity Static	242.51 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.94 in
Overall width	1.69 in
Overall weight	0.64 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Housing Color	Blue passivated
Dome diameter	1.69 in

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, black, electric-conductive
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.98 in
Body width	0.98 in
Hardness of tread (A)	80 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	2.64 in
Plate width	2.36 in
Plate hole length (Minimum)	1.57 in
Plate hole length (Maximum)	1.89 in
Plate hole width (Minimum)	1.57 in
Plate hole width (Maximum)	1.89 in
Plate hole diameter	0.25 in

AGILA

2478DYK075P60-67X60

EAN 4031582344523

Order number 00028590

Product Drawings



BETTER MOBILITY. BETTER LIFE.

