

RADIATA

994TETP080P64

EAN 4031582423471



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Radiata
Type	Turtle caster
Load capacity at 1.8 mph	3306.93 lb
Electric conductive	no
Stainless	no
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	6.54 in
Overall weight	53.05 lb

HOUSING

Housing Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Swivel interference	15.75 in

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	3.15 in
Tread width	1.57 in
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	6.89 in
Plate width	5.51 in
Plate hole length (Maximum)	5.51 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.59 in

RADIATA

994TETP080P64

EAN 4031582423471



BETTER MOBILITY. BETTER LIFE.

Product Drawings

