

ZETA STAINLESS

8670UFX160P63

EAN 4031582313536
Order number 00829521



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Zeta stainless
Type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	661.39 lb
Load capacity at 3.7 mph	529.11 lb
Stainless	✓
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	7.87 in
Overall width	3.78 in
Overall weight	6.24 lb

WHEEL

Body material	Polyamide
	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, sealed
Axle	Screwed with nut
Wheel color	Gray / non- marking
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.81 in
Body width	1.81 in
Hardness of tread (A)	64 Shore A

HOUSING

Material	Stainless steel, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Color	Stainless steel
Offset	2.17 in
Swivel radius	5.31 in
Swivel interference	10.63 in
Dome diameter	3.78 in

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Minimum)	2.91 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.91 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

ZETA STAINLESS

8670UFX160P63

EAN 4031582313536
Order number 00829521



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

