

DURATECH

MOP 160X50-Ø30

EAN 4031582320046
Order number 00801261



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.97 in
Axle hole diameter	1.18 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D
Bearing type	6306

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	5952.47 lb
Load capacity at 3.7 mph	4960.4 lb
Load capacity Static	9920.79 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	3.56 lb

DURATECH

MOP 160X50-Ø30

EAN 4031582320046
Order number 00801261



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

