

NOVATECH

FTP 140x60-Ø20 HL68 cv R190

EAN 4031582329421



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE


Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1851.88 lb
Load capacity at 3.7 mph	1543.23 lb
Electric conductive	no
Stainless	no
Load capacity Static	3086.47 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	6.09 lb

WHEEL

Tread profile	convex
Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	5.51 in
Tread width	2.36 in
Axle hole diameter	0.79 in
Hub length	2.68 in
Body width	2.36 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Bearing type	6304
Suitable for	bt




PRODUCT INFORMATION

NOVATECH

FTP 140x60-020 H268 cv R190

EAN 4031582389421

Order number 10832269



BETTER MOBILITY. BETTER LIFE.