

# ELASTECH

IFP 250X50-Ø20 HL60

EAN 4031582366280  
Order number 00838557



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                                       |
|-----------------------|---------------------------------------|
| Body material         | Aluminium                             |
| Tread material        | Elastic tire, non-marking, vulcanized |
| Bearing               | Precision ball bearing                |
| Wheel color           | Grey / non marking                    |
| Threadguards          | Without threadguard                   |
| Diameter              | 250 mm                                |
| Tread width           | 50 mm                                 |
| Axle hole diameter    | 20 mm                                 |
| Hub length            | 60 mm                                 |
| Body width            | 50 mm                                 |
| Hardness of tread (A) | 68 Shore A                            |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Elastech                      |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 500 kg                        |
| Load capacity at 6 km/h     | 400 kg                        |
| Load capacity Static        | 1000 kg                       |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 85 °C                         |
| Overall weight              | 2.37 kg                       |

# ELASTECH

IFP 250X50-Ø20 HL60

EAN 4031582366280  
Order number 00838557



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

