PRODUCT INFORMATION

AGILA

2478PJI050P41-55

EAN 4031582030013



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●●○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Agila
Type	Fixed caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	88.18 lb
Electric conductive	no
Stainless	no
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.72 in
Overall width	1.38 in
Overall weight	0.19 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Housing Color	Blue passivated
Dome diameter	1.06 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.75 in
Body width	0.75 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Square plate
Plate length	2.17 in
Plate width	2.17 in
Plate hole length (Minimum)	1.52 in
Plate hole length (Maximum)	1.73 in
Plate hole width (Minimum)	1.52 in
Plate hole width (Maximum)	1.73 in
Plate hole diameter	0.25 in

© Copyright 2026 TENTE International GmbH


AGILA


2478PJI050P41-55


EAN 4031582030013

Order number 00003898

Product Drawings







© Copyright 2026 TENTE International GmbH