

# AGILA

2477PJO075R47-24-27

EAN 4031582326314



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Agila                         |
| Type                        | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 60 kg                         |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 120 kg                        |
| Temperature range (Minimum) | -10 °C                        |
| Temperature range (Maximum) | 40 °C                         |
| Overall Height              | 103 mm                        |
| Overall weight              | 0.4 kg                        |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel Bearing      | Two ball races      |
| Housing Color       | Blue passivated     |
| Offset              | 24 mm               |
| Swivel radius       | 80 mm               |
| Swivel interference | 160 mm              |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread Material Mix    | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | Without threadguard  |
| Diameter              | 75 mm                |
| Tread width           | 25 mm                |
| Hardness of tread (A) | 87 Shore A           |

## FITTING

|                            |                                                            |
|----------------------------|------------------------------------------------------------|
| Fitting type               | Synthetic expander, square                                 |
| Expander fitting (Minimum) | 24 mm                                                      |
| Expander fitting (Maximum) | 27 mm                                                      |
| Hint                       | Please indicate required tube innerdiameter when ordering. |

# AGILA

2477PJO075R47-24-27

EAN 4031582326314

Order number 00031541

Product Drawings



BETTER MOBILITY. BETTER LIFE.

