

# AGILA CARE US

2446XSX200R26-28S

EAN 4031582388237



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                        |
|-----------------------------|----------------------------------------|
| Product name                | Agila care US                          |
| Housing type                | Swivel castor with central, total lock |
| Standard                    | similar EN12531- Hospital Bed Castors  |
| Load capacity at 3 km/h     | 150 kg                                 |
| Load capacity at 4 km/h     | 150 kg                                 |
| Electric conductive         | ✓                                      |
| Load capacity Static        | 300 kg                                 |
| Temperature range (Minimum) | -40 °C                                 |
| Temperature range (Maximum) | 80 °C                                  |
| Overall height              | 240 mm                                 |

## WHEEL

|                       |                                             |
|-----------------------|---------------------------------------------|
| Body material         | Polyamide, electric conductive              |
| Tread material        | Polyurethane, injected, electric-conductive |
| Bearing               | Precision ball bearing, sealed              |
| Threadguards          | With threadguard                            |
| Diameter              | 200 mm                                      |
| Tread width           | 32 mm                                       |
| Hardness of tread (D) | 40 Shore D                                  |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material fork       | Steel sheet, medium    |
| Fork shape          | Broad                  |
| Swivel bearing      | Precision ball bearing |
| Offset              | 62 mm                  |
| Swivel radius       | 162 mm                 |
| Swivel interference | 324 mm                 |

## FITTING

|               |                                     |
|---------------|-------------------------------------|
| Fitting type  | Stem with cam hole for profile bars |
| Bolt diameter | 28 mm                               |
| Bolt length   | 96 mm                               |