

# NOVATECH

FTP 140X54-Ø20 HL60

EAN 4031582346619  
Order number 00833009



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	140 mm
Tread width	54 mm
Axle hole diameter	20 mm
Hub length	60 mm
Body width	54 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Suitable for	jungheinrich_mic

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	840 kg
Load capacity at 6 km/h	700 kg
Load capacity Static	1400 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	2.467 kg

# NOVATECH

FTP 140X54-Ø20 HL60

EAN 4031582346619  
Order number 00833009



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

