

# AGILA

2470DIK100R05-28

EAN 4031582300628



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Agila
Tip	Okretanje Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	80 kg
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Sveukupna visina	138 mm
Ukupna težina	1,111 kg

## TOCAK

Materijal za telo	Čelik lista
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	konusi lezaj
štitnici omotaca	Sa threadguard
Prečnik	100 mm
Širina omotac	32 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

## KUCISTE

Materijal	Čelični list, srednji
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	38 mm
okretni radijus	88 mm
Otpor okretanju	176 mm

## PRILAGOĐAVANJE

Tip uklapanja	stablo, okrugla
Prečnik sraf	28 mm
Dužina sraf	45 mm

# AGILA

2470DIK100R05-28

EAN 4031582300628



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

