

OMIKRON

9258STP400P66

EAN 4031582314144
Order number 00830235



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Omikron
Housing type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	3840 kg
Load capacity at 6 km/h	3200 kg
Load capacity Static	7680 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	470 mm
Overall weight	46.95 kg

WHEEL

Body material	Sheet steel, heavy
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	400 mm
Tread width	100 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Iron forged, heavy
Fork shape	Straight

FITTING

Fitting type	Rectangular plate
Plate length	250 mm
Plate width	200 mm
Plate hole length (Maximum)	210 mm
Plate hole width (Maximum)	160 mm
Plate hole diameter	17 mm

TECHNICAL DRAWINGS

