

PRODUCT INFORMATION

# PURETECH

DIK 150x32-Ø8,1

EAN 4031582070170



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Sheet Steel
Tread Material Mix	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel Color	Blue passivated
Threadguards	With threadguard
Diameter	150 mm
Tread width	32 mm
Axle Hole Diameter	8 mm
Hub Length	36 mm
Body width	32 mm
Hardness of tread (A)	80 Shore A

## PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●●○
Corrosion Resistance	●●●○○

## CORE ATTRIBUTES

Product Name	Puretech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	0.9 kg

# PURETECH

DIK 150x32-Ø8,1

EAN 4031582070170

Order number 00000163  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

