

GALEA

5071YGH100P60-90X70

EAN 4031582353433



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------------|
| Product name | Galea |
| Type | Swivel castor with directional lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 220.46 lb |
| Electric conductive | ✓ |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 5.43 in |
| Overall weight | 1.05 lb |

WHEEL

| | |
|-----------------------|---|
| Body material | Polypropylene, electric conductive |
| Tread material | Thermoplastic rubber, electric-conductive |
| Bearing | Plain bearing |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 1.18 in |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|----------------|
| Material | Polyamide |
| Fork shape | Closed |
| Swivel bearing | Two ball races |
| Offset | 1.57 in |
| Swivel interference | 8.07 in |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 3.54 in |
| Plate width | 2.76 in |
| Plate hole length (Minimum) | 2.36 in |
| Plate hole length (Maximum) | 2.76 in |
| Plate hole width (Minimum) | 1.97 in |
| Plate hole width (Maximum) | 2.17 in |
| Plate hole diameter | 0.31 in |

PRODUCT INFORMATION

GALEA

5071YGH100P60-90X70

EAN 4031582353433



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

