

# LEVINA

5377UAP150R05-28X45

EAN 4031582363968



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●●○

Ishrana ●●●●○

otpornost na rdju ●●●●○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Levina
Tip	Okreni Tocak sa potpuna kocnica
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	40 °C
Sveukupna visina	190 mm

## TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	32 mm
Teškoća gazećeg omotac (D)	40 Šor D

## KUCISTE

Materijal	poliamid
oblik viljuska	Slim
okretni lezaj	Dve lopte
ofset	38 mm
Otpor okretanju	240 mm

## PRILAGOĐAVANJE

Tip uklapanja	stablo, okrugla
Prečnik sraf	28 mm
Dužina sraf	45 mm

Univerzalna  
nagrada DizajnDeutscher  
dizajner  
Club

# LEVINA

5377UAP150R05-28X45

EAN 4031582363968



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---



Univerzalna  
nagrada Dizajn



Deutscher  
dizajner  
Club