

MAXTECH

UAO080X30-Ø12 HL44,4 BURDEOS

EAN 4031582442274



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	80 mm
Tread width	30 mm
Axle hole diameter	12 mm
Hub length	44.4 mm
Hardness of tread (D)	60 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.13 kg

MAXTECH

UAO080X30-Ø12 HL44,4 BURDEOS

EAN 4031582442274



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

