

PRODUCT INFORMATION

DURATECH HEAT

WOO125x40-Ø20 HL60 TFR

EAN 4031582497663



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Duratech heat
Type	Wheel
Load capacity at 3 km/h	230 kg
Electric Conductive	No
Stainless	No
Load capacity Static	460 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	180 °C

WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	125 mm
Tread width	40 mm
Axle Hole Diameter	20 mm
Hub Length	60 mm