

PRODUCT INFORMATION

MAXTECH

PAO100x25-Ø6x27 + ASBUS

EAN 4031582381245



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|--------------------|---------|
| Diameter | 3.94 in |
| Tread width | 0.98 in |
| Axle hole diameter | 0.24 in |
| Hub length | 1.06 in |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------|
| Product name | Maxtech |
| Type | Wheel |
| Load capacity at 1.8 mph | 154.32 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 308.65 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 0.24 lb |