

PRODUCT INFORMATION

MAXTECH

PAO100x25-Ø6x27 + ASBUS

EAN 4031582381245



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

|                             |           |
|-----------------------------|-----------|
| Product name                | Maxtech   |
| Type                        | Wheel     |
| Load capacity at 1.8 mph    | 154.32 lb |
| Electric conductive         | no        |
| Stainless                   | no        |
| Load capacity Static        | 308.65 lb |
| Temperature range (Minimum) | -4 °F     |
| Temperature range (Maximum) | 140 °F    |
| Overall weight              | 0.24 lb   |

WHEEL

|                    |         |
|--------------------|---------|
| Diameter           | 3.94 in |
| Tread width        | 0.98 in |
| Axle hole diameter | 0.24 in |
| Hub length         | 1.06 in |