

MONO

5020PJH080L51-10 RAL9006

EAN 4031582308402
Order number 00073802



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Mono
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	104 mm
Overall weight	0.146 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	80 mm
Tread width	24 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Closed
Swivel bearing	Stem, swiveling
Colour	White aluminium (RAL9006)
Offset	34 mm
Swivel radius	74 mm
Swivel interference	148 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

PRODUCT INFORMATION

MONO

5020PJH080L51-10 RAL9006

EAN 4031582308402
Order number 00073802



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

