

NOVATECH

ETY 080x20-Ø20 EL14

EAN 4031582318524



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	308.65 lb
Load capacity at 3.7 mph	242.51 lb
Electric conductive	no
Stainless	no
Load capacity Static	617.29 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	0.66 lb

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing (RS/2RS)
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	3.15 in
Tread width	0.79 in
Axle hole diameter	0.79 in
Hub length	0.55 in
Body width	0.79 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

