

FOOTMASTER

FOOT MASTER GDR- 80-S-NYN

EAN 4031582413328



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	500 kg
Electric Conductive	No
Stainless	No
Load capacity Static	500 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	102 mm
Overall width	86 mm
Overall weight	1.2 kg

HOUSING

Housing Color	White
Offset	46 mm
Swivel radius	77.5 mm
Swivel interference	155 mm
Dome diameter	86 mm

WHEEL

Bearing	Roller bearing, damped
Wheel Color	Black
Diameter	63 mm
Tread width	30 mm
Body width	30 mm

FOOTMASTER

FOOT MASTER GDR- 80-S-NYN

EAN 4031582413328

Order number 00062083

Product Drawings



BETTER MOBILITY. BETTER LIFE.

