

# NOVATECH

ETP095X40-Ø20 HL45

EAN 4031582330403



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda Novatech

Tip Tocak

Nosivost na 3 km/h 400 kg

Statički Nosivost 800 kg

Temperaturni opseg (Minimalno) -20 °C

Opseg temperature (maksimalni) 60 °C

Ukupna težina 1,585 kg

## TOCAK

Materijal za telo Čelik, gvožđe

materijal omotaca Poliuretana, liveno

Nošenje precizini kuglicni lezaj

stitnici omotaca Sa threadguard

Prečnik 95 mm

Širina omotac 40 mm

dimenzija rupa osovina 20 mm

dužina glavčine 45 mm

Teškoća gazećeg omotac (A) 92 Šor A

Tip ležaja 6204ZV

## TEHNIČKI CRTEŽI

