

# DURATECH

UOP160X50-Ø20

EAN 4031582396140



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	160 mm
Tread width	40 mm
Axle hole diameter	20 mm
Hub length	60 mm
Hardness of tread (D)	75 Shore D

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	900 kg
Load capacity Static	1800 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	1.006 kg

# DURATECH

UOP160X50-Ø20

EAN 4031582396140



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

