

PRODUCT INFORMATION

MAXTECH

UAD100x30-Ø12 HL44,4 BURDEOS

EAN 4031582452839



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Maxtech                       |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 330.69 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 661.39 lb                     |
| Temperature range (Minimum) | -13 °F                        |
| Temperature range (Maximum) | 176 °F                        |
| Overall weight              | 0.5 lb                        |

WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide                 |
| Tread material        | Polyurethane, injected    |
| Bearing               | Roller bearing, stainless |
| Diameter              | 3.94 in                   |
| Tread width           | 1.18 in                   |
| Axle hole diameter    | 0.47 in                   |
| Hub length            | 1.75 in                   |
| Hardness of tread (D) | 42 Shore D                |

