

# FORMA

6945UFP150B33-18,7 GREY

EAN 4031582476521



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Forma
Type	Swivel castor with wheel brake
Load capacity at 3 km/h	135 kg
Temperature range (Minimum)	-18 °C
Temperature range (Maximum)	120 °C
Overall height	164 mm

## WHEEL

Body material	Polyamide
Tread hardness	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	150 mm
Tread width	18 mm
Hardness of tread (A)	60 Shore A

## HOUSING

Material fork	Zinc-die-casting / Aluminium
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Offset	57 mm
Swivel radius	137 mm

## FITTING

Fitting type	Circlip stem with hexagon socket
Bolt diameter	19 mm

# FORMA

6945UFP150B33-18,7 GREY

EAN 4031582476521



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

