

# KAPPA LOAD

9650IFP200P63

EAN 4031582472028



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |               |
|-----------------------------|---------------|
| Product name                | Kappa load    |
| Housing type                | Swivel castor |
| Load capacity at 2.5 mph    | 992.08 lb     |
| Load capacity Static        | 1984.16 lb    |
| Temperature range (Minimum) | -4 °F         |
| Temperature range (Maximum) | 176 °F        |
| Overall height              | 9.65 in       |

## WHEEL

|                       |                                       |
|-----------------------|---------------------------------------|
| Body material         | Aluminum                              |
| Tread material        | Elastic tire, non-marking, vulcanized |
| Bearing               | Precision ball bearing                |
| Axle                  | Screwed with nut                      |
| Threadguards          | Without threadguard                   |
| Diameter              | 7.87 in                               |
| Tread width           | 1.97 in                               |
| Hardness of tread (A) | 68 Shore A                            |

## HOUSING

|                     |                                        |
|---------------------|----------------------------------------|
| Material            | Cast iron, or iron forged, heavy       |
| Fork shape          | Broad, reinforced                      |
| Swivel bearing      | Deep-groove ball thrust roller bearing |
| Offset              | 2.32 in                                |
| Swivel radius       | 6.26 in                                |
| Swivel interference | 12.52 in                               |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 5.31 in           |
| Plate width                 | 4.33 in           |
| Plate hole length (Maximum) | 4.13 in           |
| Plate hole width (Minimum)  | 2.95 in           |
| Plate hole width (Maximum)  | 3.15 in           |
| Plate hole diameter         | 0.43 in           |

# KAPPA LOAD

9650IFP200P63

EAN 4031582472028



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

