

DELTA TWIN

9948ICP160P63-92A

EAN 4031582477993



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Delta twin
Housing type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	750 kg
Load capacity at 6 km/h	600 kg
Load capacity Static	1500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	70 °C
Overall height	210 mm
Overall weight	4.406 kg

WHEEL

Body material	Aluminium
Tread material	Ultratech Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	160 mm
Tread width	50 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Iron forged, heavy
Fork shape	Twin wheel housing

FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	137 mm
Plate hole diameter	11 mm

DELTATWIN

9948ICP160P63-92A

EAN 4031582477993



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

