

# ANIKA

5920UAI075L51-10 DOM18

EAN 4031582455458



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Anika
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	77.2 mm
Overall width	41.5 mm
Overall weight	0.11 kg

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	75 mm
Tread width	11 mm

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	24 mm
Swivel radius	64.4 mm
Swivel interference	128.8 mm
Dome diameter	18 mm

## FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm



# ANIKA

5920UAI075L51-10 DOM18

EAN 4031582455458



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

