

ELASTECH

UFR100X34-Ø12 HL44,4 AZUL

EAN 4031582452891



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.249 kg

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	34 mm
Axle hole diameter	12 mm
Hub length	44.4 mm
Hardness of tread (A)	64 Shore A

ELASTECH

UFR100X34-Ø12 HL44,4 AZUL

EAN 4031582452891



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

