

# NOVATECH

FTP 100X40-Ø15 HL40

EAN 4031582329360



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	420 kg
Nosivost na 6 km/h	350 kg
Statički Nosivost	700 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,94 kg

## TOCAK

Materijal za telo	Ливено Гвожђе
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	100 mm
Širina omotac	40 mm
dimenzija rupa osovina	15 mm
dužina glavčine	40 mm
Širina tela	40 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D
Tip ležaja	6002
Pogodno za	linde_jungh_mic

# NOVATECH

FTP 100X40-Ø15 HL40

EAN 4031582329360



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

