

# DURATECH

TOP 085X60-Ø20 HL60

EAN 4031582331165  
Order number 00832610



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	3.35 in
Tread width	2.36 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	2.36 in
Hardness of tread (D)	75 Shore D
Bearing type	6204

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1433 lb
Load capacity at 3.7 mph	1146.4 lb
Load capacity Static	2866.01 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	1.13 lb

# DURATECH

TOP 085X60-Ø20 HL60

EAN 4031582331165  
Order number 00832610



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

