

NOVATECH

FTX140X50-Ø20 HL55-A

EAN 4031582339963



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Ливено Гвожђе
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj, zaprecaceno
stitnici omotaca	Sa threadguard
Prečnik	140 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
duzina glavčine	55 mm
Teškoća gazećeg omotac (A)	92 Šor A
Tip ležaja	6006 2RS
Tip zaptivke	A
Pogodno za	bt_linde

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Nosivost na 3 km/h	630 kg
Statički Nosivost	1260 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	2,474 kg

NOVATECH

FTX140X50-Ø20 HL55-A

EAN 4031582339963



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

