

NOVATECH

ETY 060X20-Ø20 HL12

EAN 4031582318463
Order number 00830217



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing (RS/2RS)
Wheel color	Honey yellow (RAL1005)
Diameter	60 mm
Tread width	20 mm
Axle hole diameter	20 mm
Hub length	12 mm
Body width	20 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity at 6 km/h	80 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.14 kg

NOVATECH

ETY 060X20-Ø20 HL12

EAN 4031582318463
Order number 00830217



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

