

PRODUCT INFORMATION

NOVATECH

RK.ETP100x40-Ø47x14

EAN 4031582369588



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Undefined
Tread Material Mix	Polypropylene, soft
Diameter	100 mm
Tread width	40 mm
Hardness of tread (A)	92 Shore A
Ball bearing diameter	47 mm
Ball bearing width	14 mm

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Load capacity at 3 km/h	500 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1000 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C

NOVATECH

RK.ETP100x40-Ø47x14

EAN 4031582369588

Order number 00839713
Product Drawings



BETTER MOBILITY. BETTER LIFE.

