

NOVATECH

FTX140X50-Ø20 HL55-A

EAN 4031582339963



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing, sealed
Threadguards	With threadguard
Diameter	5.51 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.17 in
Hardness of tread (A)	92 Shore A
Bearing type	6006 2RS
Sealing type	A
Suitable for	bt_linde

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Load capacity at 1.8 mph	1388.91 lb
Load capacity Static	2777.82 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	5.45 lb

NOVATECH

FTX140X50-Ø20 HL55-A

EAN 4031582339963



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

