

# AGILA

2477PJP100P30-13

EAN 4031582335118  
Order number 00006340



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila                         |
| Housing type                | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 1.8 mph    | 220.46 lb                     |
| Load capacity Static        | 440.92 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall height              | 5.31 in                       |
| Overall width               | 2.36 in                       |
| Overall weight              | 1.7 lb                        |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Wheel color           | Silver gray (RAL7001)  |
| Threadguards          | With threadguard       |
| Diameter              | 3.94 in                |
| Tread width           | 1.26 in                |
| Body width            | 1.26 in                |
| Hardness of tread (A) | 87 Shore A             |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material            | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Color               | Blue passivated     |
| Offset              | 1.71 in             |
| Swivel radius       | 5.16 in             |
| Swivel interference | 10.31 in            |
| Dome diameter       | 2.36 in             |

## FITTING

|                    |                                                            |
|--------------------|------------------------------------------------------------|
| Fitting type       | Bolt hole                                                  |
| Bolt hole diameter | 0.51 in                                                    |
| Hint               | Castors can be mounted with standard screws of any length. |

## PRODUCT INFORMATION

# AGILA

2477PJP100P30-13

EAN 4031582335118  
Order number 00006340



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

