

PRODUCT INFORMATION

# NOVATECH

ETP085x80-Ø25 HL82

EAN 4031582438062



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Steel, iron
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	85 mm
Tread width	80 mm
Axle Hole Diameter	25 mm
Hub Length	80 mm
Hardness of tread (A)	92 Shore A
Bearing type	6205

## PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

## CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Load capacity at 3 km/h	700 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C

# NOVATECH

ETP085x80-Ø25 HL82

EAN 4031582438062



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

