

PRODUCT INFORMATION

MAXTECH

PNR389x85-Ø25 HL74 TFR

EAN 4031582400359



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread Material Mix	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	389 mm
Tread width	85 mm
Axle Hole Diameter	25 mm
Hub Length	74 mm

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Load capacity at 3 km/h	75 kg
Electric Conductive	No
Stainless	No
Load capacity Static	150 kg
Overall weight	1.95 kg

MAXTECH

PNR389x85-Ø25 HL74 TFR

EAN 4031582400359



BETTER MOBILITY. BETTER LIFE.

Product Drawings

