

# ALPHA STAINLESS

8478UFC160P63

EAN 4031582422504



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Alpha stainless
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Stainless	✓
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall height	7.87 in
Overall weight	4.07 lb

## WHEEL

Body material	Polyamide
	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.81 in
Hardness of tread (A)	64 Shore A

## HOUSING

Material	Stainless steel, heavy
Fork shape	Broad

## FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.53 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

# ALPHA STAINLESS

8478UFC160P63

EAN 4031582422504



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

