

STYLEA

5923UAI055L51-10 BIAŁY

EAN 4031582477085



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------------------|
| Product name | Stylea |
| Type | Swivel castor with intermittend brake |
| Load capacity at 1.8 mph | 88.18 lb |
| Load capacity Static | 176.37 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 2.24 in |
| Overall width | 1.46 in |
| Overall weight | 1.43 lb |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 2.17 in |
| Tread width | 0.43 in |
| Hardness of tread (A) | 92 Shore A |

HOUSING

| | |
|---------------------|--------------------|
| Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 1.85 in |
| Swivel interference | 3.7 in |
| Dome diameter | 0.71 in |

FITTING

| | |
|--------------------|----------------------------|
| Fitting type | Blind hole for B10 fitting |
| Bolt hole diameter | 0.39 in |



STYLEA

5923UAI055L51-10 BIAŁY

EAN 4031582477085



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

