

PURETECH

JYX 150x32-Ø8,3 clip

EAN 4031582319972



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	330.69 lb
Electric conductive	Yes
Stainless	no
Load capacity Static	661.39 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	1.97 lb

WHEEL

Tread hardness	soft
Body material	Zinc die-cast
Tread material	Solid rubber, black, electric-conductive
Bearing	Precision ball bearing, sealed
Wheel color	Metallic
Threadguards	With threadguard
Diameter	5.91 in
Tread width	1.26 in
Axle hole diameter	0.33 in
Hub length	1.4 in
Body width	1.26 in
Hardness of tread (A)	75 Shore A

PURETECH

JYX 150x32-Ø8,3 clip

EAN 4031582319972

Order number 00024890
Product Drawings



BETTER MOBILITY. BETTER LIFE.

