

PRODUCT INFORMATION

# ELASTECH HEAT

IDP100x30-8 HL50

EAN 4031582460667



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Aluminium
Tread Material Mix	Damping, heat resistant
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	30 mm
Axle Hole Diameter	8 mm
Hub Length	50 mm
Hardness of tread (A)	80 Shore A

## PERFORMANCE

Roll Performance	●●●●●
Movement Noise	●●○○○
Attrition	●●●○○
Corrosion Resistance	●●○○○

## CORE ATTRIBUTES

Product Name	Elastech heat
Type	Wheel
Load capacity at 3 km/h	200 kg
Electric Conductive	No
Stainless	No
Load capacity Static	400 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	280 °C
Overall weight	0.29 kg