



BETTER MOBILITY. BETTER LIFE.

S70-10X25 / 11 DRILLED STEM

EAN 4031582411911



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Overall height	6 mm
Overall weight	0.051 kg

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	25 mm