

LINEA LIGHT

5927UAP075S70-M10X15 HN EN12528 RAL7001

EAN 4031582414806



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Linea light
Housing type	Swivel castor with total lock
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	86 mm
Overall width	55 mm
Overall weight	0.227 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	75 mm
Tread width	15 mm

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	23 mm
Swivel radius	82 mm
Swivel interference	164 mm
Thread diameter	0 mm

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	15 mm



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award

PRODUCT INFORMATION

LINEA LIGHT


5927UAP075S70-M10X15 HN EN12528 RAL7001

EAN 4031582414806



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award