

ELASTECH

EEZ 200X75-Ø100 DG

EAN 4031582318333
Order number 00830872



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------------|
| Body material | Steel, iron |
| Tread hardness | soft |
| Tread material | Elastic tire, black, vulcanized |
| Bearing | Borehole, unmachined |
| Wheel color | Jet black (similar RAL9005) |
| Diameter | 200 mm |
| Tread width | 75 mm |
| Axle hole diameter | 100 mm |
| Hub length | 75 mm |
| Body width | 75 mm |
| Hardness of tread (A) | 68 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|------------------------------|
| Product name | Elastech |
| Type | Wheel |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h | 600 kg |
| Load capacity at 6 km/h | 500 kg |
| Load capacity Static | 1000 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 85 °C |
| Overall weight | 2.306 kg |

ELASTECH

EEZ 200X75-Ø100 DG

EAN 4031582318333
Order number 00830872



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

